

HEDI

Cable drum plastic, Type: 25V



Order data

Order number	081125 25V
GTIN	4003644013258
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. For use in dry environments.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

IP Index of Protection: IP 20

Rated power unrolled: 3500 (16 A) W

Cable class: H05VV-F

Cable structure: 3G1.5

Material cable: PVC red

Cable length: 25 m

Number of sockets: 4

Technical description

Cable structure	3G1.5
-----------------	-------

Material cable	PVC red
Type	25V
Cable length	25 m
AC supply voltage	250 V
Rated power unrolled	3500 (16 A) W
Cable class	H05VV-F
IP Index of Protection	IP 20
Number of sockets	4
Material of body	Plastic
Power supply	Mains operated
Diagnostic system present	no
Type of product	Cable drum