

## USB charging adaptor, Type: 2



### Order data

Order number	081149 2
GTIN	4008496066162
Item class	08C

### Description

#### Version:

- **Total output: 38 W for optimised, fast charging**
- **Latest GN technology**
- **Technology trend: Power Delivery and Quick Charge for fast, intelligent charging**
- **AC input: 100-240 V ~ 1.0 A 50-60 Hz**
- **1 pc. USB Type C port: 5 V/3 A; 9 V/2.22 A; 12 V/1.67 A (max. 20 W)**
- **1 pc. USB A QC port: 5 V/3 A; 9 V/2 A; 12 V/1.5 A (max. 18 W)**
- **Simultaneously charge up to 2 devices**
- **Super-light, very handy and compact**
- **Modern, high-quality design**
- **Proven VARTA quality ensured**

### Technical description

Number of charging slots for USB	2
Nominal voltage	100 - 240 V
Length	80 mm
Height	195 mm

## Data sheet

Mains frequency	50 - 60 Hz
Maximum number of charging points	2
Width	35 mm
Manufacturer's designation	VARTA Speed Charger 38 W
Type of product	Battery charger