

Garant**Side milling cutter with collar Width $a_p = 5$ mm, $\varnothing D$: 63mm****Order data**

Order number	218562 63
GTIN	4045197462428
Item class	210

Description**Version:**

Side milling cutters of robust special steel for reduced vibration.

Application:

For milling grooves and slots. For flat or non-flat slot base.

Spare part:

No. 219949 (TX9; 2.0 Nm).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size IP9**.

Side milling cutters available up to $\varnothing D = 200$ mm.

Technical description

Collar length L_1	15 mm
Mounting bore \varnothing	22 mm
Overall length L_{tot}	50 mm
suitable indexable insert	SNHX
maximum cutting depth $a_{e,max}$	10.5 mm

Number of effective inserts Z_{eff}	4
Cutting edge $\varnothing D_c$	63 mm
Collar $\varnothing d_1$	40 mm
Number of indexable inserts	8
Shank type	with bore
Through-coolant	no
Tool exchange	PowerCard
ISO code indexable insert	SN.. 1103
Pack of insert screws	219949 (IP9; 2.0 Nm)
Type of product	Side milling cutter

Accessories

Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2
Pack of insert screws 10 pieces	219949
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 9IP	674252 9IP