

Garant

Blade HSS width $a_p = 2.2$ mm, $\varnothing D$ / number of teeth Z: 80/5mm



Order data

Order number	218442 80/5
GTIN	4045197534132
Item class	21P

Description

Version:

High-performance parting-off milling cutter system with choice of either collar and **low-cost steel blade** or collar and **high-precision temperature-resistant HSS blade**.

Application:

For slitting and parting off milling. For high repetition accuracy in series production it is preferable to use the HSS blade.

Attention:

Please order the assembly key No. 279940 separately.

Note:

Side and parting-off milling cutters available up to $\varnothing D = 200$ mm.
HSS spare blades can be reordered as accessories.

Technical description

Cutting edge $\varnothing D_c$	80 mm
suitable indexable insert	XC.. 1119
Set of securing screws	219985

Number of cutting edges Z	5
Shank type	with bore
Tool material	HSS
Type of product	Side milling cutter

Accessories

Securing screw set 10 pieces	219985
------------------------------	--------