

Garant

Parallel arbor, without through-coolant, Weldon shank, for cutter head Ø D: 16mm



Order data

Order number	210555 16
GTIN	4045197522658
Item class	21Z

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milling depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Clamping wrench = No. 219987.

Insert for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

Reach L_1	40 mm
External $\varnothing d_1$	15.8 mm
for cutter head $\varnothing D$	16 mm
recommended tightening torque	15 Nm
Overall length L	100 mm
Shank $\varnothing D_s$	25 mm
Series	TopCut
Adapter	Weldon shank
Type of product	Threaded copy mill arbor

