

## Garant

### Parallel arbor, without through-coolant, Weldon shank, for cutter head Ø D: 20mm



#### Order data

Order number	210555 20
GTIN	4045197522665
Item class	21Z

#### Description

##### Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

**System radial run-out ≤ 10 µm** due to the combination of taper and flat face.

##### Note:

**Maximum milling depth** =  $L_1 + l$ ;  $l$  = see dimensions of the screw-in heads: No. 210050 – 210410.

Clamping wrench = No. 219987.

Insert for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

#### Technical description

External Ø $d_1$	19.8 mm
for cutter head Ø D	20 mm
Reach $L_1$	51 mm
recommended tightening torque	25 Nm
Overall length L	110 mm
Shank Ø $D_s$	25 mm
Series	TopCut
Adapter	Weldon shank
Type of product	Threaded copy mill arbor

