


Garant

Parallel arbor, without through-coolant, Weldon shank, for cutter head Ø D: 25mm



Order data

Order number	210555 25
GTIN	4045197522672
Item class	21Z

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out ≤ 10 µm due to the combination of taper and flat face.

Note:

Maximum milling depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Clamping wrench = No. 219987.

Insert for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

Reach L_1	62 mm
External $\varnothing d_1$	24.8 mm
for cutter head $\varnothing D$	25 mm
recommended tightening torque	35 Nm
Overall length L	120 mm
Shank $\varnothing D_s$	25 mm
Series	TopCut
Adapter	Weldon shank
Type of product	Threaded copy mill arbor

