

Garant

**Parallel arbor, with through-coolant, Weldon shank, for cutter head Ø D:
12mm**



Order data

Order number	210557 12
GTIN	4045197557742
Item class	21Z

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

for cutter head Ø D	12 mm
Reach L_1	26 mm
External Ø d_1	11.8 mm
recommended tightening torque	10 Nm
Overall length L	80 mm
Shank Ø D_s	20 mm
Series	TopCut
Adapter	Weldon shank
Through-coolant	yes

Type of product

Threaded copy mill arbor