

Yale

Hollow piston cylinder YCS, Pressure force / stroke (t / mm): 33/150



Order data

Order number	086070 33/150
GTIN	4025092150927
Item class	08Y

Description

Version:

Yale hydraulic equipment is made of high quality **CrMo steel** for significantly higher strength in the "elastic range" resulting in a **very long working life**. All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all 700 bar hydraulic systems.

Due to their **central through hole**, these cylinders are suitable for applications where a high tensile force has to be exerted via a **threaded spindle**, quick-release connection.

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

Application:

Pre-loading of anchor fastenings, **pressing bearings, axles, and shafts in and out, pulling off** gear wheels and pulleys, and pulling or moving heavy fabrications.

Supplied with:

Supplied with 3/8 NPT pressure connection. Equipment is supplied ready to use, including connection sleeve, hardened steel load piece (head) and securing thread **without** connection hoses and adaptors.

Note:

Closed systems are pre-mounted ex works, filled and air bled.

Hydraulic hand pump see No. 086050, hydraulic hose No. 086081.

Technical description

Length retracted	343 mm
------------------	--------

Oil volume	716 ml
Cylinder external Ø	114 mm
Through hole Ø	33 mm
Lifting height	150 mm
maximum compressive force	335 kN
Weight	21 kg
Type of product	Hydraulic cylinder