

Garant
Tapered arbor, SK 40, for cutter head Ø D: 16mm

Order data

Order number	210577 16
GTIN	4045197557926
Item class	21Z

Description
Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

Overhang dimension A	81 mm
for cutter head Ø D	16 mm
External Ø d_1	15.8 mm
Reach L_1	62 mm
recommended tightening torque	15 Nm
Arbor size	40 mm
Series	TopCut
Adapter	SK 40
Through-coolant	yes

Type of product

Threaded copy mill arbor