

Garant

Solid carbide tapered arbor long, Plain shank, for cutter head Ø D: 16mm



Order data

| | |
|--------------|---------------|
| Order number | 210570 16 |
| GTIN | 4045197522788 |
| Item class | 21Z |

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

With plain shank (for HSC machining). **Tolerance = h6.**

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

| | |
|---------------------------------|--------------------------|
| Shank $\varnothing D_s$ h6 | 25 mm |
| Reach L_1 | 103 mm |
| for cutter head $\varnothing D$ | 16 mm |
| External $\varnothing d_1$ | 15.8 mm |
| recommended tightening torque | 15 Nm |
| Overall length L | 170 mm |
| Series | TopCut |
| Adapter | Plain shank |
| Through-coolant | yes |
| Type of product | Threaded copy mill arbor |

