


**Garant**
**Parallel arbor vibration damped, Plain shank, for cutter head Ø D: 25mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 210551 25     |
| GTIN         | 4045197662309 |
| Item class   | 21Z           |

**Description**
**Version:**

Precision-ground arbor for GARANT TopCut screw-in heads.

**System radial run-out  $\leq 10 \mu\text{m}$**  due to the combination of taper and flat face.

With solid carbide core, without clamping flat.

**Note:**

**Maximum milled depth** =  $L_1 + l$ ;  $l$  = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

**Technical description**

|                                 |                          |
|---------------------------------|--------------------------|
| External $\varnothing d_1$      | 24.8 mm                  |
| Shank $\varnothing D_5 h6$      | 25 mm                    |
| for cutter head $\varnothing D$ | 25 mm                    |
| Reach $L_1$                     | 63 mm                    |
| recommended tightening torque   | 35 Nm                    |
| Overall length $L$              | 120 mm                   |
| Series                          | TopCut                   |
| Adapter                         | Plain shank              |
| Through-coolant                 | yes                      |
| Type of product                 | Threaded copy mill arbor |

