

## Garant

**Tapered arbor, with through-coolant, Weldon shank, for cutter head Ø D: 16mm**



### Order data

Order number	210567 16
GTIN	4045197557810
Item class	21Z

### Description

#### Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

**System radial run-out  $\leq 10 \mu\text{m}$**  due to the combination of taper and flat face.

#### Note:

**Maximum milled depth** =  $L_1 + l$ ;  $l$  = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

### Technical description

Reach $L_1$	56 mm
External $\varnothing d_1$	15.8 mm
for cutter head $\varnothing D$	16 mm
recommended tightening torque	15 Nm
Overall length $L$	115 mm
Shank $\varnothing D_s$	25 mm
Series	TopCut
Adapter	Weldon shank
Through-coolant	yes

Type of product

Threaded copy mill arbor