

Garant
Parallel arbor vibration damped, Plain shank, for cutter head Ø D: 10mm

Order data

Order number	210551 10
GTIN	4045197658852
Item class	21Z

Description
Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

With solid carbide core, without clamping flat.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

External $\varnothing d_1$	9.8 mm
Shank $\varnothing D_5 h6$	10 mm
for cutter head $\varnothing D$	10 mm
Reach L_1	30 mm
recommended tightening torque	5 Nm
Overall length L	70 mm
Series	TopCut
Adapter	Plain shank
Through-coolant	yes
Type of product	Threaded copy mill arbor

