

HEDI

Cable drum plastic, Type: 50R



Order data

Order number	081125 50R
GTIN	4003644013449
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. With spring-loaded covers. For **short-term** use in the open air. Satisfies DGUV I 203-005 (formerly BGI 600).

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

IP Index of Protection: IP 44

Rated power unrolled: 3500 (16 A) W

Cable class: H05RR-F

Cable structure: 3G1.5

Material cable: Rubber

Cable length: 50 m

Number of sockets: 3

Technical description

Cable length	50 m
Cable class	H05RR-F
AC supply voltage	250 V
Rated power unrolled	3500 (16 A) W
Cable structure	3G1.5
Material cable	Rubber
Type	50R
IP Index of Protection	IP 44
Number of sockets	3
Material of body	Plastic
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum