

Garant

Solid carbide parallel arbor stub, Plain shank, for cutter head Ø D: 10mm



Order data

Order number	210561 10
GTIN	4045197558077
Item class	21Z

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

With plain shank (for HSC machining). **Tolerance = h6.**

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

for cutter head Ø D	10 mm
Shank Ø D _s h6	12 mm
Reach L ₁	46 mm
External Ø d ₁	9.8 mm
recommended tightening torque	5 Nm
Overall length L	95 mm
Series	TopCut
Adapter	Plain shank
Through-coolant	yes
Type of product	Threaded copy mill arbor

