

Garant
Arbor parallel, HSK-A 63, for cutter head Ø D: 10mm

Order data

Order number	210580 10
GTIN	4045197522856
Item class	21Z

Description
Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

Overhang dimension A	47 mm
External $\varnothing d_1$	9.8 mm
for cutter head $\varnothing D$	10 mm
Reach L_1	21 mm
recommended tightening torque	5 Nm
Series	TopCut
Adapter	HSK-A 63

Through-coolant	yes
Type of product	Threaded copy mill arbor