

Garant

Parallel arbor, without through-coolant, Weldon shank, for cutter head Ø D: 12mm



Order data

Order number	210555 12
GTIN	4045197522641
Item class	21Z

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out ≤ 10 µm due to the combination of taper and flat face.

Note:

Maximum milling depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Clamping wrench = No. 219987.

Insert for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

External Ø d_1	11.8 mm
Reach L_1	26 mm
for cutter head Ø D	12 mm
recommended tightening torque	10 Nm
Overall length L	80 mm
Shank Ø D_s	20 mm
Series	TopCut
Adapter	Weldon shank
Type of product	Threaded copy mill arbor

