



HELISLOT side milling cutter without flange, \varnothing DC / Zeff: 125/14mm



Order data

| | |
|--------------|---------------|
| Order number | 227722 125/14 |
| GTIN | 7291075430790 |
| Item class | 19D |

Description

Version:

Economical machining of grooves and T-slots. Achieve different slot widths with only one insert size thanks to the insert seat concept with staggered teeth formation. Square inserts with positive rake angle for efficient and gentle machining. Very reliable process thanks to optimised insert support in the seat.

Spare part:

Pack of insert screws No. **229695 3** (TX9; 2.0 Nm).

Technical description

| | |
|---|----------|
| Number of indexable inserts | 14 |
| Mounting bore \varnothing | 40 mm |
| Series | HELISLOT |
| Cutting edge \varnothing D _c | 125 mm |
| Overall length L _{tot} | 14 mm |
| maximum cutting depth a _{e,max} | 34 mm |

| | |
|--|---------------------|
| Number of effective inserts Z_{eff} | 14 |
| Slot width a_p | 10 mm |
| Manufacturer's designation | SDN D125-10-40-XN09 |
| Shank type | with bore |
| Type of product | Side milling cutter |

Accessories

| | |
|--------------------------------------|----------|
| Set of insert screws 5 pieces Type 3 | 229695 3 |
|--------------------------------------|----------|