



HELISLOT side milling cutter with flange, \varnothing DC / Zeff: 125/6mm



Order data

Order number	227712 125/6
GTIN	7291075311242
Item class	19D

Description

Version:

Economical machining of grooves and T-slots. Achieve different slot widths with only one insert size thanks to the insert seat concept with staggered teeth formation. Square inserts with positive rake angle for efficient and gentle machining. Very reliable process thanks to optimised insert support in the seat.

Spare part:

Pack of insert screws No. **229697 1** (IP15; 4.8 Nm).

Technical description

Series	HELISLOT
Mounting bore \varnothing	32 mm
Collar length L_1	30.5 mm
Number of effective inserts Z_{eff}	6
Number of indexable inserts	12
Overall length L_{tot}	45 mm

Cutting edge $\varnothing D_c$	125 mm
maximum cutting depth $a_{e\max}$	33 mm
Slot width a_p	16 mm
Manufacturer's designation	FDN D125-16-32-XN13
Shank type	with bore
Type of product	Side milling cutter

Accessories

Insert screw Type 1	229697 1
---------------------	----------