

**Garant****Side milling cutter with collar Width  $a_p = 12$  mm,  $\varnothing D$ : 50mm****Order data**

Order number	218567 50
GTIN	4045197530479
Item class	210

**Description****Version:**

Side milling cutters of robust special steel for reduced vibration.

**Application:**

For milling grooves and slots. For flat or non-flat slot base.

**Spare part:**

No. 219984 (TX15; 2.2 Nm).

**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size IP15**.

Side milling cutters available up to  $\varnothing D = 200$  mm.

**Technical description**

suitable indexable insert	SNHX
Collar $\varnothing d_1$	32 mm
Cutting edge $\varnothing D_c$	50 mm
Number of effective inserts $Z_{\text{eff}}$	2
maximum cutting depth $a_{e \text{ max}}$	8.5 mm

Overall length $L_{tot}$	50 mm
Mounting bore $\varnothing$	16 mm
Collar length $L_1$	15 mm
Number of indexable inserts	4
Shank type	with bore
Through-coolant	no
Tool exchange	PowerCard
ISO code indexable insert	SN.. 1207
Pack of insert screws	219984 (IP15; 2.2 Nm)
Type of product	Side milling cutter

## Accessories

Set of insert screws 10-piece	219984
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2