

**Cable drum sheet steel, Type: 50R****Order data**

Order number	081105 50R
GTIN	4003644004751
Item class	08B

Description**Version:**

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. For use in dry environments.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Technical description

Cable structure	3G1.5
Cable class	H05RR-F
AC supply voltage	250 V
Material cable	Rubber
Rated power unrolled	3500 (16 A) W

Data sheet

Cable length	50 m
IP Index of Protection	IP 20
Number of sockets	4
Material of body	Sheet metal
Power supply	Mains operated
Diagnostic system present	no
Type of product	Cable drum