

# Yale

## Spare hydraulic hose HHC, Length: 2m



### Order data

|              |               |
|--------------|---------------|
| Order number | 086080 2      |
| GTIN         | 4025092155380 |
| Item class   | 08Y           |

### Description

#### Version:

With hydraulic coupling No. 086085 size M1 (cylinder end) and screw-in connectors 3/8-NPT (pump end). External  $\varnothing$  14 mm; internal  $\varnothing$  6.3 mm (nominal bore); bursting pressure 2800 bar; minimum bending radius  $R = 100$  mm.

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

#### Note:

**Closed systems are pre-mounted ex works, filled and air bled.**

### Technical description

|                 |                       |
|-----------------|-----------------------|
| Length          | 2 m                   |
| Type of product | Hydraulic accessories |