

Garant**Torque screwdriver, fixed setting, set torque: 2,2N·m****Order data**

Order number	211750 2,2
GTIN	4045197553201
Item class	21B

Description**Version:**

Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.

Function:

When the torque is reached the screwdriver triggers **with clearly audible and perceptible signal**. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.

Application:

In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank**, e.g. **Torx Plus® bit** No. **674252**. Ideal for precise tightening of indexable inserts to the specified torque.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

Supplied **without** bit.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

set torque	2.2 Nm
Blade length	50 mm
Torque measuring accuracy	±10 %
Bit socket	D 6,3
Bit socket	F 6.3
Adjustable trigger value	non-adjustable
Measurement process	Torque
Connection format	Bit holder 1/4 inch
Standard	DIN EN ISO 6789
Reversible reading	Nm
Overall length L	107 mm
Setting the trigger value	preset
Feedback	triggering
Trigger principle	Mechanical long travel release
Direction of tightening	Right-hand tightening
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

Accessories

"TQ-Station" – storage station for torque screwdrivers	659964
--	--------