




TANGGRIP TNFFA-IQ axial grooving toolholder reinforced, right-hand, Ø range / cut DAXN-DAXX: 65-80mm



Order data

Order number	274202 65-80
GTIN	7291075310818
Item class	26D

Description

Application:

For face grooving.

Suitable for:

Cutting inserts No. 274422 – 274226.

Attention:

Please order the assembly key No. 279952 separately.

Technical description

Grooving depth t_{max}	27 mm
Series	TANG-GRIP
Groove width w	3 mm
Overall length L	90 mm
WB_2	18.5 mm
WF	9.5 mm
Shank height h_s	32 mm
Functional height h_1	24.8 mm
Manufacturer's designation	TNFFA 65R-3IQ
Overhang	27 mm

Application type	right-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder