



TANGGRIP TNFFH-IQ axial grooving toolholder, right-hand, Ø range / cut DAXN-DAXX: 150-700mm



Order data

Order number	274204 150-700
GTIN	7291075310795
Item class	26D

Description

Version:

With two insert pockets.

Application:

For face grooving.

Suitable for:

Inserts No. 274422 – 274226.

Attention:

Please order the assembly key No. 279952 separately.

Technical description

Groove width w	6 mm
Overall length L	150 mm
Grooving depth t_{max}	35 mm
Series	TANG-GRIP
WF	3.3 mm
WB_2	5.2 mm
Functional height h_1	24.8 mm
Shank height h_5	32 mm
Manufacturer's designation	TNFFH 150R-6IQ

Overhang	35 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder