



HELIGRIP HELI toolholder, right-hand, Shank size / groove width w: 20/3mm



Order data

Order number	273766 20/3
GTIN	7291075031645
Item class	26D

Description

Version:

Straight design (Figure 1).

Application:

For groove turning, grooving and parting off.

Suitable for:

Inserts No. 273403 – 273413.

Technical description

WF	18.8 mm
Groove width w	3 mm
Overall length L	140 mm
Head length L ₁	29 mm
Series	HELI-GRIP
Shank size	20 mm
CWX	4.76 mm
WB	2.4 mm
CUTDIA	40 mm
Insert size	32 mm
Manufacturer's designation	HELIR 2020-3T20

Application type	right-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder