



## HELIGRIP HELI toolholder, right-hand, Shank size / groove width w: 16/3mm



### Order data

Order number	273766 16/3
GTIN	7291075031911
Item class	26D

### Description

**Version:**

Straight design (Figure 1).

**Application:**

For groove turning, grooving and parting off.

**Suitable for:**

Inserts No. 273403 – 273413.

### Technical description

Head length $L_1$	30 mm
Shank size	16 mm
Grooving depth $t_{max}$	12 mm
Overall length L	135 mm
Groove width w	3 mm
WF	14.8 mm
Series	HELI-GRIP
WB	2.4 mm
CUTDIA	32 mm
CWX	3.18 mm
Manufacturer's designation	HELIR 1616-3T12

Application type	right-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder