



HELIGRIP HELI toolholder, right-hand, Shank size / groove width w: 16/4mm



Order data

| | |
|--------------|---------------|
| Order number | 273766 16/4 |
| GTIN | 7291075032130 |
| Item class | 26D |

Description

Application:

For groove turning, grooving and parting off.

Suitable for:

Inserts No. 273403 – 273413.

Technical description

| | |
|----------------------------|-----------------|
| Series | HELI-GRIP |
| Grooving depth t_{max} | 12 mm |
| WF | 14.4 mm |
| Head length L_1 | 29 mm |
| Groove width w | 4 mm |
| Shank size | 16 mm |
| Overall length L | 135 mm |
| CWX | 4.76 mm |
| CUTDIA | 32 mm |
| WB | 3.2 mm |
| Manufacturer's designation | HELIR 1616-4T12 |
| Application type | right-hand |

| | |
|-------------------------|------------|
| Through-coolant | no |
| axial grooving possible | yes |
| Type of product | Toolholder |