



## HELIGRIP HELI toolholder, right-hand, Shank size / groove width w: 25/5mm



### Order data

Order number	273766 25/5
GTIN	7291075031454
Item class	26D

### Description

#### Application:

For groove turning, grooving and parting off.

#### Suitable for:

Inserts No. 273403 – 273413.

### Technical description

WF	22.9 mm
Series	HELI-GRIP
Head length L <sub>1</sub>	42 mm
Groove width w	5 mm
Shank size	25 mm
Overall length L	140 mm
WB	4.2 mm
CWX	5 mm
CUTDIA	50 mm
Insert size	16 mm
Manufacturer's designation	HELIR 2525-5T25
Application type	right-hand

Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder