



HELIGRIP HELI toolholder, right-hand, Shank size / groove width w: 20/4mm



Order data

Order number	273766 20/4
GTIN	7291075031683
Item class	26D

Description

Application:

For groove turning, grooving and parting off.

Suitable for:

Inserts No. 273403 – 273413.

Technical description

WF	18.4 mm
Series	HELI-GRIP
Groove width w	4 mm
Shank size	20 mm
Head length L ₁	42 mm
Overall length L	140 mm
CUTDIA	50 mm
CWX	4.76 mm
WB	3.2 mm
Manufacturer's designation	HELIR 2020-4T25
Application type	right-hand
Through-coolant	no

axial grooving possible	yes
Type of product	Toolholder