



PENTAIQGRIP PCH-IQ toolholder, right-hand, Shank size / insert size: 25/40mm



Order data

Order number	273576 25/40
GTIN	7291075317978
Item class	26D

Description

Application:

First choice for parting off up to diameter 40 mm. Grooving is possible.

Suitable for:

Inserts No. 273580 – 273581.

Technical description

Series	PENTAIQGRIP
CWN-CWX	3 - 3.2 mm
Overall length L	135 mm
HBH	8 mm
Shank size	25 mm
WF	23.7 mm
Head length L ₁	33.3 mm
H	43.5 mm
HBL	33.6 mm
Insert size	12 mm
Manufacturer's designation	PCHR 25-D40-3-IQ
Application type	right-hand

Through-coolant	no
axial grooving possible	no
Type of product	Toolholder