



PENTAIQGRIP PCH-IQ toolholder, right-hand, Shank size / insert size: 20/40mm



Order data

Order number	273576 20/40
GTIN	7291075318005
Item class	26D

Description

Application:

First choice for parting off up to diameter 40 mm. Grooving is possible.

Suitable for:

Inserts No. 273580 – 273581.

Technical description

Head length L ₁	33.3 mm
WF	18.7 mm
CWN-CWX	3 - 3.2 mm
Series	PENTAIQGRIP
Overall length L	135 mm
Shank size	20 mm
HBH	13 mm
H	43.5 mm
HBL	35.6 mm
Insert size	16 mm
Manufacturer's designation	PCHR 20-D40-3-IQ
Application type	right-hand

Through-coolant	no
axial grooving possible	no
Type of product	Toolholder