



PENTAIQGRIP PCH-IQ toolholder, right-hand, Shank size / insert size: 20/32mm



Order data

| | |
|--------------|---------------|
| Order number | 273576 20/32 |
| GTIN | 7291075318319 |
| Item class | 26D |

Description

Application:

First choice for parting off up to diameter 40 mm. Grooving is possible.

Suitable for:

Inserts No. 273580 – 273581.

Technical description

| | |
|----------------------------|------------------|
| H | 33.6 mm |
| Head length L ₁ | 28.4 mm |
| CWN-CWX | 2 - 2.4 mm |
| HBH | 6 mm |
| Series | PENTAIQGRIP |
| WF | 19.5 mm |
| Shank size | 20 mm |
| Overall length L | 120 mm |
| HBL | 29.5 mm |
| Manufacturer's designation | PCHR 20-D32-2-IQ |
| Application type | right-hand |
| Through-coolant | no |

| | |
|-------------------------|------------|
| axial grooving possible | no |
| Type of product | Toolholder |