



## PENTAIQGRIP PCH-IQ toolholder, left-hand, Shank size / insert size: 25/40mm



### Order data

Order number	273577 25/40
GTIN	7291075318029
Item class	26D

### Description

#### Application:

First choice for parting off up to diameter 40 mm. Grooving is possible.

#### Suitable for:

Inserts No. 273580 – 273581.

### Technical description

HBH	8 mm
Overall length L	135 mm
Shank size	25 mm
WF	23.7 mm
H	43.5 mm
Head length L <sub>1</sub>	33.3 mm
CWN-CWX	3 - 3.2 mm
Series	PENTAIQGRIP
HBL	33.6 mm
Manufacturer's designation	PCHL 25-D40-3-IQ
Application type	left-hand
Through-coolant	no

axial grooving possible	no
Type of product	Toolholder