



HELIGRIP HELI toolholder, left-hand, Shank size / groove width w: 16/3mm



Order data

Order number	273767 16/3
GTIN	7291075031928
Item class	26D

Description

Version:

Straight design (Figure 1).

Application:

For groove turning, grooving and parting off.

Suitable for:

Inserts No. 273403 – 273413.

Technical description

WF	14.8 mm
Series	HELI-GRIP
Shank size	16 mm
Groove width w	3 mm
Overall length L	135 mm
Grooving depth t_{max}	12 mm
Head length L_1	30 mm
WB	2.4 mm
CWX	3.18 mm
CUTDIA	32 mm
Manufacturer's designation	HELIL 1616-3T12

Application type	left-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder