



## HELIGRIP HELI toolholder, left-hand, Shank size / groove width w: 16/4mm



### Order data

Order number	273767 16/4
GTIN	7291075032116
Item class	26D

### Description

#### Application:

For groove turning, grooving and parting off.

#### Suitable for:

Inserts No. 273403 – 273413.

### Technical description

Shank size	16 mm
WF	14.4 mm
Groove width w	4 mm
Overall length L	135 mm
Head length L <sub>1</sub>	29 mm
Series	HELI-GRIP
Grooving depth t <sub>max</sub>	12 mm
CWX	4.76 mm
WB	3.2 mm
CUTDIA	32 mm
Manufacturer's designation	HELIL 1616-4T12
Application type	left-hand

Through-coolant	no
axial grooving possible	yes
Type of product	Toolholder