



HELIGRIP HELI toolholder, left-hand, Shank size / groove width w: 20/3mm



Order data

| | |
|--------------|---------------|
| Order number | 273767 20/3 |
| GTIN | 7291075031638 |
| Item class | 26D |

Description

Version:

Straight design (Figure 1).

Application:

For groove turning, grooving and parting off.

Suitable for:

Inserts No. 273403 – 273413.

Technical description

| | |
|----------------------------|-----------------|
| Head length L ₁ | 29 mm |
| Shank size | 20 mm |
| Series | HELI-GRIP |
| Overall length L | 140 mm |
| Groove width w | 3 mm |
| WF | 18.8 mm |
| CUTDIA | 40 mm |
| WB | 2.4 mm |
| CWX | 4.76 mm |
| Manufacturer's designation | HELIL 2020-3T20 |
| Application type | left-hand |

| | |
|-------------------------|------------|
| Through-coolant | no |
| axial grooving possible | yes |
| Type of product | Toolholder |