



HELIGRIP HELI toolholder, left-hand, Shank size / groove width w: 20/5mm



Order data

Order number	273767 20/5
GTIN	7291075031713
Item class	26D

Description

Application:

For groove turning, grooving and parting off.

Suitable for:

Inserts No. 273403 – 273413.

Technical description

Head length L ₁	42 mm
Shank size	20 mm
WF	17.9 mm
Overall length L	140 mm
Groove width w	5 mm
Series	HELI-GRIP
CUTDIA	50 mm
WB	4.2 mm
CWX	5 mm
Manufacturer's designation	HELIL 2020-5T25
Application type	left-hand
Through-coolant	no

axial grooving possible	yes
Type of product	Toolholder