



## PENTACUT PCH-17 toolholder, left-hand, Shank size / insert size: 10/17mm



### Order data

Order number	273951 10/17
GTIN	7291075389487
Item class	26D

### Description

#### Application:

For flush work on workpiece shoulders for groove widths of 0.25 mm – 3.18 mm.

#### Suitable for:

Inserts No. 273956 – 273959.

#### Note:

For right-hand toolholders use right-hand inserts, for left-hand toolholders use left-hand inserts.

### Technical description

Series	PENTACUT
Head length $L_1$	17 mm
Shank size	10 mm
Overall length L	120 mm
Grooving depth $t_{max}$	4 mm
HBH	2 mm
OAH	15.6 mm
Insert size	17 mm
Manufacturer's designation	PCHLS 10-17
Application type	left-hand
Through-coolant	no

axial grooving possible	no
Type of product	Screw-on toolholder