



HELI-GRIP HFH compact toolholder strengthened, left-hand, Ø area/ cut DAXN-DAXX: 140-240mm



Order data

| | |
|--------------|----------------|
| Order number | 273769 140-240 |
| GTIN | 7291075033083 |
| Item class | 26D |

Description

Application:

For axial grooving and facing.

Suitable for:

Cutting inserts No. 273403 – 273413.

Note:

For left-hand compact toolholders, use left-hand inserts (type HGPL or HFPL).

Technical description

| | |
|----------------------------|------------------|
| WF | 25.6 mm |
| Head length L_1 | 44 mm |
| OAH | 37 mm |
| Series | HELI-GRIP |
| Groove width w | 4 mm |
| H | 25 mm |
| Grooving depth t_{max} | 25 mm |
| Overall length L | 150 mm |
| Manufacturer's designation | HFHL 25-140-4T25 |
| B | 25 mm |

| | |
|-------------------------|---------------------|
| Application type | left-hand |
| Through-coolant | no |
| axial grooving possible | yes |
| Type of product | Screw-on toolholder |