



HELI-GRIP HFH compact toolholder strengthened, left-hand, Ø area/ cut DAXN-DAXX: 100-140mm



Order data

Order number	273769 100-140
GTIN	7291075033069
Item class	26D

Description

Application:

For axial grooving and facing.

Suitable for:

Cutting inserts No. 273403 – 273413.

Note:

For left-hand compact toolholders, use left-hand inserts (type HGPL or HFPL).

Technical description

OAH	37 mm
Head length L_1	44 mm
Series	HELI-GRIP
H	25 mm
Groove width w	4 mm
WF	25.74 mm
Overall length L	150 mm
Grooving depth t_{max}	25 mm
Manufacturer's designation	HFHL 25-100-4T25
B	25 mm

Application type	left-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Screw-on toolholder