



HELI-GRIP HFH compact toolholder strengthened, left-hand, Ø area/ cut DAXN-DAXX: 40-48mm



Order data

Order number	273769 40-48
GTIN	7291075032840
Item class	26D

Description

Application:

For axial grooving and facing.

Suitable for:

Cutting inserts No. 273403 – 273413.

Note:

For left-hand compact toolholders, use left-hand inserts (type HGPL or HFPL).

Technical description

WF	20.6 mm
Series	HELI-GRIP
H	20 mm
OAH	31 mm
Head length L_1	44 mm
Groove width w	4 mm
Overall length L	140 mm
Grooving depth t_{max}	25 mm
Manufacturer's designation	HFHL 20-40-4T25
B	20 mm

Application type	left-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Screw-on toolholder