



MINCUT boring bar, right-hand, Shank \varnothing / insert size: 12/8mm



Order data

Order number	270420 12/8
GTIN	7291075262391
Item class	26l

Description

Version:

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

Application:

For face grooving and groove turning in the diameter range 8 mm – 17 mm.

Suitable for:

Inserts No. 270422 – 270429.

Technical description

Shank $\varnothing D_s$	12 mm
Series	MINCUT
Overall length L	102.5 mm
Centre offset L_3	7.4 mm
Insert size	8 mm
Head length l_2	12.5 mm
Radial width f_2	5.5 mm
Function width f_1	1.4 mm
Cooling $\varnothing d_s$	5 mm
Radius R	3.8 mm
Manufacturer's designation	MIFHR 12C-8

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar