



MINCUT boring bar, right-hand, Shank \varnothing / insert size: 16/10mm



Order data

| | |
|--------------|---------------|
| Order number | 270420 16/10 |
| GTIN | 7291075262414 |
| Item class | 26I |

Description

Version:

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to perform.

Application:

For face grooving and groove turning in the diameter range 8 mm – 17 mm.

Suitable for:

Inserts No. 270422 – 270429.

Technical description

| | |
|--------------------------------------|---------|
| Shank \varnothing D _s | 16 mm |
| Centre offset L ₃ | 11.2 mm |
| Insert size | 10 mm |
| Series | MINCUT |
| Overall length L | 90 mm |
| Head length l ₂ | 17.2 mm |
| Function width f ₁ | 2.4 mm |
| Radial width f ₂ | 7.5 mm |
| Cooling \varnothing d ₅ | 6 mm |
| Radius R | 4.6 mm |

| | |
|----------------------------|--------------|
| Manufacturer's designation | MIFHR 16C-10 |
| Application type | right-hand |
| Through-coolant | yes |
| Type of product | Boring bar |