




DOVEIQGRIP THD toolholder, right-hand, Shank size / groove width w: 25/10mm



Order data

Order number	274140 25/10
GTIN	7291075316667
Item class	26D

Description

Version:

For external groove machining.

Technical description

OAL	170 mm
WB	9.2 mm
CDX	20 mm
Shank size	25 mm
Groove width w	10 mm
WF	20.4 mm
HBL	30 mm
Series	DOVEIQGRIP
HBH	8 mm
Manufacturer's designation	THDR 2525-10T20-IQ
Overhang	20 mm
Application type	right-hand
Through-coolant	yes

Data sheet

axial grooving possible	no
Type of product	Screw-on toolholder