




DOVEIQGRIP THD toolholder, right-hand, Shank size / groove width w: 40/16mm



Order data

Order number	274140 40/16
GTIN	7291075316735
Item class	26D

Description

Version:

For external groove machining.

Technical description

CDX	50 mm
WB	14.8 mm
Groove width w	16 mm
OAL	180 mm
WF	32.6 mm
Series	DOVEIQGRIP
Shank size	40 mm
Manufacturer's designation	THDR 4040-16T50-IQ
Overhang	50 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Screw-on toolholder

