

## Extension cable, 250 V, Type: 25N



### Order data

Order number	081182 25N
GTIN	4007123014651
Item class	08B

### Description

#### Version:

**Certified for exterior use and for use in humid environments (IP44).** Resistant to oil, petrol, UV radiation.

**Neoprene rubber cable** with splash-proof rubber plug and socket.

#### Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away.

### Technical description

Type	25N
Cable structure	3G1.5
Cable class	H07RN-F
Material cable	Neoprene
Cable length	25 m
impact-resistant and splash-proof	Category 2 (K2) to BGI

IP Index of Protection	IP 44
Power supply	Mains operated
Plug type, input	F
Product name attribute	250 V
AC supply voltage	250 V
Type of product	Extension cable

---

## Accessories

CableFix cable suspension system Type S	081191 S
CableFix cable suspension system Type L	081191 L
CableFix cable suspension system Type XL	081191 XL