



Pen torch WORK PEN 200 R, Type: WORK-PEN



Order data

Order number	081566 WORK-PEN
GTIN	5708997351277
Item class	08C

Description

Version:

200-lumen rechargeable LED pen light with **continuous dimming function** and **integrated magnets**.

WORK PEN 200 R is a **rechargeable pen light** and is part of the updated FLASHLIGHT product range. The perfect work light for professional inspection tasks – always at hand!

The LED pen light provides extremely **powerful** illumination from both the light head (up to 200 lumens) and the spotlight at the top, which provides astonishing illumination of **150 lumens** for such a small pen light. The side-mounted button switch also enables effortless one-handed operation.

The light is also equipped with a continuous dimming function from **10%** to **100%**, meaning that the light output can be adjusted to the respective work task. The robust aluminium construction provides **comfortable handling** and the **slim** and compact design enables access to the most inaccessible and narrow areas.

WORK PEN 200 R comes with **magnets integrated in the clip** and on the bottom of the light for hanging or storage. This means increased flexibility and easy placement of the light when both hands need to be free for the work task.

The pen light is simply charged with a **USB cable**, thus eliminating the need to interrupt what you are doing and waste time replacing the rechargeable batteries. The **battery indicator** on the front shows the charging status. Includes a holder clip for the breast pocket.

The WORK PEN 200 R's design is unique and protected by the EU design patent.

The WORK PEN 200 R is supplied without a power supply unit and charging cable.

Function:

IP30: Protected against penetration by foreign bodies with $\varnothing > 2.5$ mm. However, tools and wires should be kept away and there is no protection against water.

Technical description

Power supply	Mains operated
Illumination time	10 h
IP Index of Protection	IP 30
Spread angle	105 degrees
Illumination	20 - 200 lm
Bulb	LED module
Colour temperature	6000 K
Battery voltage	3.7 V
Number of rechargeable batteries contained	1
Battery capacity	0.75 Ah
Type of rechargeable battery	Lithium-ion
Type of product	Inspection lamp