

HEDI

Cable drum plastic, Type: 40B



Order data

Order number	081125 40B
GTIN	4003644002320
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. PU armoured cable Plus.

With spring-loaded covers. For **continuous** use in the open air. Satisfies DGUV I 203-005 (formerly BGI 600).

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

IP Index of Protection: IP 44

impact-resistant and splash-proof: Category 2 (K2) to BGI

Rated power unrolled: 3500 (16 A) W

Cable class: H07BQ-F

Cable structure: 3G1.5

Material cable: Armoured cable

Cable length: 40 m

Number of sockets: 3

Technical description

Cable structure	3G1.5
AC supply voltage	250 V
Rated power unrolled	3500 (16 A) W
Cable class	H07BQ-F
Cable length	40 m
Material cable	Armoured cable
Type	40B
IP Index of Protection	IP 44
impact-resistant and splash-proof	Category 2 (K2) to BGI
Material of body	Plastic
Number of sockets	3
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum